


# intermediate position attachment SLG-Z-8/12-A

Part number: 525680

FESTO

For linear drive SLG



## Data sheet

Feature	Value
Assembly position	Any
Design structure	Stop as rotary drive system
Position detection	For proximity sensor
Operating pressure	1 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Product weight	33.5 g
Mounting type	With through-hole and dowel pin
Pneumatic connection	M3
Material stops	Steel, nickel-plated
Material seals	PUR
Material housing	Aluminium Hard anodised