



# Proximity Sensor

## SMT-8F-NS-24V-K2,5-OE

Part number: 525909

FESTO

Electrical, contactless, NPN, for drive units with 8 mm sensor slot, top mounting, with cable.



## Data sheet

Feature	Value
Operating voltage range DC	10 ... 30 V
Switch output	NPN
Switching element function	Normally open contact
Cable length	2.5 m
Electrical connection	3-core Cable
Design	for T-slot
Short circuit strength	Yes
Polarity protected	for all electrical connections
Operating status display	Yellow LED
Switch-off time	7 ms
Switch-on time	$\leq 0.2$ ms
Max. contact rating DC	3 W
Residual current	0.1 mA
Voltage drop	1.8 V
Protection class	IP65 IP67
Ambient temperature	-5 ... 60 °C -20 ... 60 °C
Product weight	30 g
Reproducibility of switching value	+/- 0,1 mm
Mounting type	Clamped in T-slot
Materials note	Free of copper and PTFE
Materials information, housing	PA
Materials information, cable sheaths	PUR