



Proximity Sensor

SMT-10F-PS-24V-K2,5L-OE

Part number: 525915

FESTO

Electrical, contactless, PNP, for drive units with 10 mm sensor slot, top mounting, with cable.



Data sheet

Feature	Value
Design	for round slot
Authorisation	C-Tick c UL us - Listed (OL)
CE mark (see declaration of conformity)	to EU directive for EMC
Materials note	Free of copper and PTFE
Ambient temperature	-20 ... 60 °C
Switch output	PNP
Switching element function	Normally open contact
Reproducibility of switching value	+/- 0,1 mm
Switch-on time	≤ 0.33 ms
Switch-off time	0.3 ms
Max. contact rating DC	6 W
Voltage drop	2 V
Residual current	0.06 mA
Short circuit strength	Yes
Operating voltage range DC	5 ... 30 V
Polarity protected	for all electrical connections
Electrical connection	Cable 3-core
Connector exit direction	axial
Cable length	2.5 m
Materials information, cable sheaths	PUR
Mounting type	Insertable Clamped in round slot
Tightening torque	0.2 Nm
Product weight	15 g
Materials information, housing	PA
Operating status display	Yellow LED
Ambient temperature	-5 ... 60 °C
Protection class	IP65 IP67