

**PAN-4x0,75-SI-P**

Plastic tubing

Data sheet

Part no.: 526186

Page:1

<b>Feature</b>	<b>Data/description</b>
Nominal size of tubing	<b>4</b>
Internal diameter	<b>2,9 mm</b>
Outside diameter	<b>4 mm</b>
Bending radius min.	<b>18 mm</b>
Operating pressure min.	<b>-0,95 bar</b>
Operating pressure max. at 20°C	<b>14,5 bar</b>
Operating pressure max. at 30°C	<b>12,5 bar</b>
Operating pressure max. at 40°C	<b>10,5 bar</b>
Operating pressure max. at 50°C	<b>9,5 bar</b>
Operating pressure max. at 60°C	<b>8,5 bar</b>
Operating pressure max. at 70°C	<b>7,5 bar</b>
Operating pressure max. at 80°C	<b>7 bar</b>
Suitable for vacuum	<b>Yes</b>
Minimum ambient temperature	<b>-30 °C</b>
Maximum ambient temperature	<b>80 °C</b>
Material of tubing	<b>TPE-A</b>
Product weight per meter	<b>0,0062 kg/m</b>
Color	<b>Silver</b>