

PAN-16x2-SI-P

Plastic tubing

Data sheet

Part no.: 526191

Page:1

Feature	Data/description
Nominal size of tubing	16
Internal diameter	12 mm
Outside diameter	16 mm
Bending radius min.	94 mm
Operating pressure min.	-0,95 bar
Operating pressure max. at 20°C	13,5 bar
Operating pressure max. at 30°C	11,5 bar
Operating pressure max. at 40°C	9,5 bar
Operating pressure max. at 50°C	9 bar
Operating pressure max. at 60°C	8 bar
Operating pressure max. at 70°C	7 bar
Operating pressure max. at 80°C	6,5 bar
Suitable for vacuum	Yes
Minimum ambient temperature	-30 °C
Maximum ambient temperature	80 °C
Material of tubing	TPE-A
Product weight per meter	0,0915 kg/m
Color	Silver