

# Filter regulator LFR-N1/8-D7-5M-MICRO


Part number: 526281  
Product to be discontinued

FESTO

With threaded connection plate and pressure gauge, manual condensate drain

This product is only available if ordered from the Festo Corporation, USA.

Type to be discontinued. Available until 2016. See Support Portal for alternative products.



## Data sheet

Feature	Value
Size	Micro
Series	D
Assembly position	Vertical
Grade of filtration	5 µm
Condensate drain	manual rotary
Max. condensate volume	3 cm <sup>3</sup>
Operating pressure	1 ... 10 bar
Max. pressure hysteresis	0.3 bar
Standard nominal flow rate	410 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases
Corrosion resistance classification CRC	2
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	124 g
Mounting type	Optional Line installation With mounting bracket
Pneumatic connection, port 1	NPT1/8-27
Pneumatic connection, port 2	NPT1/8-27
Materials note	Conforms to RoHS
Materials information, housing	Wrought Aluminium alloy
Materials information for bowl	PC