


# Servo motor MTR-AC-100-3S-GA

Part number: 526733

FESTO

With gearbox.



## Data sheet

Feature	Value
Torsional backlash	≤ 0.05 deg
Type of gear unit	Planetary gear unit
Gear unit ratio	4:1
Rotor position sensor	Resolver
Temperature monitoring	PTC resistor
Nominal output speed gear unit for 50% ED	575 1/min
Nominal output speed gear unit for 100% ED	387 1/min
Max. speed	5,320 1/min
Nominal rotary speed	4,300 1/min
Continuous open-circuit current	6.7 A
Insulation protection class	F
Motor constant	0.711 Nm/A
Nominal motor power	1,417 W
Nominal voltage DC	325 V
Nominal motor current	5 A
Peak current	20 A
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Storage temperature	-10 ... 60 °C
Relative air humidity	Max. 90%
Protection class	IP54
Ambient temperature	-40 ... 40 °C
Authorisation	c UL us - Recognized (OL)
Overall mass moment of inertia at power take-off	42.2 kgcm <sup>2</sup>
Gear-unit output torque	13.8 Nm
Gear unit efficiency	0.98
Mass moment of inertia of gear unit	0.6 kgcm <sup>2</sup>
Mass moment of inertia of rotor	2.6 kgcm <sup>2</sup>
Nominal torque	3.53 Nm
Peak torque	12.2 Nm
Standstill torque	4.74 Nm
Torsional resistance	≤ 4.5 Nm/arc
Permissible axial shaft load	9,000 N
Permissible radial shaft load	4,000 N
Product weight	8,980 g
Electrical connector system	Plug