



MS6-LDM

Diaphragm air dryer

Feature	Data/description
Size	6
Series	MS
Assembly position	Vertical +/- 5°
Design structure	Membrane dryer
Bowl guard	integrated as metal shell
Inlet pressure 1	3 - 8,5 bar
Standard nominal flow rate	200 - 400 l/min
Operating medium	Air quality class 1:7:1 per ISO 8573-1
Pressure dew-point reduction	13 °C
Corrosion resistance classification CRC	2
Storage temperature	-20 - 55 °C
Medium temperature	5 - 55 °C
Ambient temperature	5 - 55 °C
Mounting type	Optional Line installation with accessories
Materials information, housing	Aluminium die cast
Materials information for bowl	Wrought Aluminium alloy