

lubricator MS4N-LOE

Part number: 527702

FESTO

With NPT thread



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	4
Series	MS
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	30 ml
Bowl guard	Plastic guard integrated as metal shell
Operating pressure	1 ... 12 bar
Minimum flow rate for lubricator function	40 l/min
Standard nominal flow rate	1,100 ... 2,200 l/min
Authorisation	c UL us - Recognized (OL)
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	-10 ... 60 °C
Product weight	194 g
Mounting type	Line installation with accessories Optional
Materials note	Conforms to RoHS
Material housing	Aluminium die cast
Material bowl	Wrought Aluminium alloy