


lubricator MS6-LOE-3/8-R

Part number: 529783

FESTO

Plastic bowl with plastic bowl guard, direction of flow: from left to right.



Data sheet

Feature	Value
Size	6
Series	MS
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	75 cm ³
Bowl guard	Plastic guard
Operating pressure	1 ... 16 bar
Minimum flow rate for lubricator function	50 l/min
Standard nominal flow rate	5,300 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Food-safe	See Supplementary material information
Medium temperature	-10 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	-10 ... 60 °C
Product weight	600 g
Mounting type	Line installation with accessories Optional
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Materials note	Conforms to RoHS
Material housing	Aluminium die cast
Material bowl	PC