

coupling

EAMC-40-66-11-11

Part number: 530090

FESTO

For electromechanical drive with stepper motor



Data sheet

| Feature | Value |
|------------------------|------------------------|
| Holder diameter 1 | 11 mm |
| Holder diameter 2 | 11 mm |
| Size | 40 |
| Nominal length | 66 mm |
| Assembly position | Any |
| Max. speed | 6,500 1/min |
| PWIS conformity | VDMA24364-B2-L |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 ... 60 °C |
| Mass moment of inertia | 42.3 kgmm ² |
| Transferable torque | 21 Nm |
| Product weight | 139 g |
| Materials note | Conforms to RoHS |