

sealing ring OK-3/8

Part number: 531773

FESTO

To seal (screw-in) threaded pins.



Data sheet

| Feature | Value |
|---|---|
| Based on the standard | ISO 16030 |
| Operating pressure for entire temperature range | -0.095 ... 1 MPa |
| Operating pressure complete temperature range | -0.95 ... 10 bar |
| Operating pressure for entire temperature range | -13.775 ... 145 psi |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -10 ... 60 °C |
| Manual tightening at ambient temperature | Yes |
| Nominal tightening torque | 12.5 Nm |
| Tolerance for nominal tightening torque | ± 20 % |
| Product weight | 0.44 g |
| Pneumatic connection | G3/8 |
| Materials note | Conforms to RoHS |
| Material stops | PA-reinforced |
| Material seals | TPE-U(PU) |