


micro filter cartridge MS6-LFM-A

Part number: 532909

FESTO

For MS series, degree of filtration: 0.01 µm



Data sheet

Feature	Value
Size	6
Based on the standard	ISO 12500-1 ISO 12500-3
Series	MS
Grade of filtration	0.01 µm
Max. standard flow rate for air quality class	900 l/min
Min. standard flow rate for air quality class	135 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [6:-:4] Inert gases
PWIS conformity	VDMA24364-B1/B2-L
Air purity class at output	Compressed air to ISO 8573-1:2010 [3:-:2]
Fractional efficiency (0.1 - 0.5 µm)	99.995 %
MPPS	0.05 µm
MPPS filter efficiency	99.95 %
Residual oil content	0.01 mg/m ³