

spiral plastic tubing PUN-10X1,5-SG-2,4-BL-1/4

Part number: 533463

FESTO

Highly flexible, fibre-reinforced, hydrolysis resistant to a great extent



Data sheet

Feature	Value
Working length	2.4 m
Outside diameter	9.5 mm
Block length	0.889 m
Bending radius relevant for flow rate	50 mm
Inside diameter	6.4 mm
Coil diameter	42 mm
Number of windings	21
Temperature dependent operating pressure	-0.95 ... 15 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 ... 60 °C
Nominal tightening torque	11 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	180 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	Male thread G1/4
Colour	blue
Shore hardness	A 87 +/- 3
Material of connecting thread	Brass Nickel plated
Material buckling protection	POM
Material tubing	TPE-U(PU)