

# spiral plastic tubing PUN-12X2-SG-4,8-BL-3/8

Part number: 533466

FESTO

Highly flexible, fibre-reinforced, hydrolysis resistant to a great extent



## Data sheet

Feature	Value
Working length	4.8 m
Outside diameter	11.7 mm
Block length	1.172 m
Bending radius relevant for flow rate	65 mm
Inside diameter	7.9 mm
Coil diameter	51 mm
Number of windings	41
Temperature dependent operating pressure	-0.95 ... 13 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 ... 60 °C
Nominal tightening torque	12.5 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	480 g
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	Male thread G3/8
Colour	blue
Shore hardness	A 87 +/- 3
Material of connecting thread	Brass Nickel plated
Material buckling protection	POM
Material tubing	TPE-U(PU)