

# Push-in bulkhead connector QSS-F-8

Part number: 533911

FESTO



## Data sheet

| Feature                                       | Value                                                    |
|-----------------------------------------------|----------------------------------------------------------|
| Size                                          | Standard                                                 |
| Nominal size                                  | 7 mm                                                     |
| Design structure                              | Push/pull principle                                      |
| Operating pressure complete temperature range | -0.95 ... 16 bar                                         |
| Operating medium                              | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium            | Lubricated operation possible                            |
| Corrosion resistance classification CRC       | 3                                                        |
| Food safety                                   | to manufacturer's declaration                            |
| Ambient temperature                           | 0 ... 150 °C                                             |
| Authorisation                                 | Germanischer Lloyd                                       |
| Product weight                                | 34.6 g                                                   |
| Pneumatic connection, port 1                  | for tubing, 8mm outside diameter                         |
| Pneumatic connection, port 2                  | for tubing, 8mm outside diameter                         |
| Materials note                                | Conforms to RoHS                                         |
| Materials information, housing                | Brass<br>Chromium and nickel plated                      |
| Materials information for thread seal         | FPM                                                      |
| Materials information for tubing seal         | FPM                                                      |