



VAPB-3/8-F-63-F0304-CR

Ball valve

Feature	Data/description
Nominal size	12 mm
Type of actuation	pneumatic
Sealing principle	soft
Assembly position	Any
Design structure	Ball valve
Valve function	2/2
Nominal operating pressure	63 bar
Standard nominal flow rate	350 l/min
Operating medium	Neutral liquid Water Neutral gases Compressed air
Corrosion resistance classification CRC	3
Medium temperature	-20 - 150 °C
Product weight	200 g
Mounting type	Line installation
Pneumatic connection, port 1	Rp3/8
Pneumatic connection, port 2	Rp3/8
Materials information for seals	PTFE
Materials information, housing	Stainless steel casting