


control cable

KES-MC-1-SUB-9-2,5

Part number: 537923
Product to be discontinued

FESTO

[Suitable for MTR-DCI-...](#)



Data sheet

Feature	Value
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	9
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	10
Electrical connection 2, occupied pins/wires	9
Operating voltage range DC	0 ... 24 V
Cable length	2.5 m
Cable attribute	Suitable for chain link trunking
Bending radius, fixed cable installation	≥ 28 mm
Bending radius, flexible cable installation	≥ 51 mm
Cable diameter	6.8 mm
Cable structure	10x0,14 Shielded
Nominal conductor cross-section	0.14 mm ²
Wire ends	Pin terminal
Protection class	IP54
Note on degree of protection	in assembled condition
Ambient temperature	0 ... 50 °C
Materials note	Contains PWIS substances
Corrosion resistance classification CRC	0 - No corrosion stress