

# supply cable KPWR-MC-1-SUB-9HC-2,5

Part number: 537931  
Product to be discontinued

FESTO

[Suitable for MTR-DCI-...](#)



## Data sheet

Feature	Value
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	Angular
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	Sub-D Mixed
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
Operating voltage range DC	24 ... 48 V
Cable length	2.5 m
Cable attribute	Suitable for chain link trunking
Bending radius, flexible cable installation	$\geq 64$ mm
Cable diameter	8.6 mm
Cable structure	2x1,5 Shielded
Nominal conductor cross-section	1.5 mm <sup>2</sup>
Wire ends	Pin terminal
Protection class	IP54
Note on degree of protection	in assembled condition
Ambient temperature	0 ... 50 °C