

Silencer extension UOMS-1/4

Part number: 538436

FESTO

To further reduce the level of noise, up to four silencer elements can be fitted on top of one another.



Data sheet

Feature	Value
Type of seal on screw-in stud	Without seal
Assembly position	Any
Design structure	Open silencer
Operating pressure, vacuum generator	0 ... 8 bar
Operating pressure of vacuum generator	0 ... 0.8 MPa 0 ... 116 psi
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	0 ... 60 °C
Mounting type	Detenting
Product weight	8.6 g
Material of silencer insert	PU foam
Material of threaded plug	POM
Material housing	POM
Material inner tube	Wrought Aluminium alloy