

connecting cable KVI-CP-3-WS-WD-8

Part number: 540331

FESTO

For valve terminal CPV and CP electrical components CTEC.



Data sheet

Feature	Value
Additional functions	Contact 3 of socket 1 mm leading
Cable identification	with accessories
Connection frequency	500
Product weight	399.4 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plug socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M9x0,5
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Plug
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	M9x0,5
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
Electrical connection 2, type of mounting	Screw lock
Operating voltage range DC	0 ... 30 V
Acceptable current load at 40°C	1.6 A
Note on acceptable current load at 40°C	2.3 A for 0.34 mm ² 3.6 A for 0.49 mm ²
Surge strength	1.5 kV
Cable length	8 m
Cable attribute	Suitable for energy chains
Test conditions of cable	Test conditions on request
Bending radius, flexible cable installation	≥ 75 mm
Cable diameter	5.5 mm
Cable structure	2x0,25+2x0,34+0,49 Shielded
Nominal conductor cross-section	0.25 mm ² 0.34 mm ² 0.49 mm ²
Protection class	IP65 IP67
Note on degree of protection	in assembled condition
Ambient temperature	-20 ... 80 °C
Ambient temperature with flexible cable installation	-5 ... 80 °C
CE mark (see declaration of conformity)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS

Feature	Value
Degree of contamination	1
Corrosion resistance classification CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	light grey
Material housing	PA PBT TPE-U(PUR)
Housing colour	Black
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated bronze Brass, gold-plated
Material insulation	TPE-U(PUR)