


axial kit EAMM-A-D60-52C

Part number: 543164

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	17 Nm
Product weight	1,020 g
Interface code, actuator	D60A D60C
Interface code, motor in	52C
Materials note	Contains PWIS substances Conforms to RoHS