



vertical pressure supply plate

VABF-S3-1-P1A3-G14

Part number: 544434

FESTO

For valve terminal VDMA-01/02, standard port pattern to 15407-1, for mounting between manifold sub-base and valve.



Data sheet

| Feature | Value |
|---|---|
| Width | 26 mm |
| Based on the standard | ISO 15407-1 |
| Assembly position | Any |
| Pneumatic vertical stacking | Alternative pressure supply for 1 |
| Operating pressure | -0.9 ... 10 bar |
| Standard nominal flow rate | 1,000 l/min |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Protection class | IP65 NEMA 4 |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 201 g |
| Vertical stacking type of mounting | on manifold block on individual sub-base |
| Materials note | Conforms to RoHS |
| Material housing | Aluminium die cast |