


vertical pressure supply plate

VABF-S2-1-P1A3-N38

Part number: 546094

FESTO

For valve terminal VTSA, standard port pattern to 5599-1, 5599-2, for mounting between manifold sub-base and valve.



Data sheet

Feature	Value
Width	43 mm
Based on the standard	ISO 5599-2
Assembly position	Any
Pneumatic vertical stacking	Alternative pressure supply for 1
Operating pressure MPa	-0.09 ... 1 MPa
Operating pressure	-0.9 ... 10 bar
Standard nominal flow rate	1,300 l/min
CE mark (see declaration of conformity)	to EU directive pressure reservoirs
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP65 NEMA 4
Ambient temperature	-5 ... 50 °C
Product weight	340 g
Vertical stacking type of mounting	on manifold block on individual sub-base
Materials note	Conforms to RoHS
Material housing	Aluminium die cast