

Plastic tubing

PUN-5/32X1/32-U-BL-500


Part number: 546677

FESTO

standard O.D. tubing, suitable for QS and QB push-in fittings.

This product is only available if ordered from the Festo Corporation, USA.

Old part no. 13028627



Data sheet

Feature	Value
Outer diameter, inches	5/32
Inner diameter, inches	3/32
Min. bending radius	0.202 "
Temperature dependent operating pressure	-14 ... 150 Psi
Operating medium	Filtered compressed air Vacuum
Ambient temperature	-68 ... 140 °F
Product weight according to length	0.103 oz/ft
Colour	blue
Shore hardness	A 98 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	TPE-U(PU)