

spiral plastic tubing

PAS-4I-6E-5

Part number: 548143
Product to be discontinued

FESTO

Type to be discontinued. Available until 2017. See Support Portal for alternative products.



Data sheet

Feature	Value
Working length	5 m
Outside diameter	6 mm
Block length	0.3 m
Inside diameter	4 mm
Coil diameter	50 mm
Number of windings	46
Temperature dependent operating pressure	-0.95 ... 17.5 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Ambient temperature	-30 ... 80 °C
Product weight	135 g
Colour	blue
Shore hardness	D 55 +/-3
Materials note	Free of copper and PTFE
Materials information for tubing	PA