

shock absorber DYEF-M6-Y1F

Part number: 548372

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | M6 |
| Stroke | 3.1 mm |
| Cushioning | Pneumatic cushioning with fixed metallic stop |
| Assembly position | Any |
| Position detection | No |
| Max. impact speed | 0.8 m/s |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 ... 60 °C |
| Cushioning length | 3.1 mm |
| Max. energy consumption per stroke | 0.03 J |
| Product weight | 5.1 g |
| Mounting type | with lock nut |
| Materials note | Conforms to RoHS |
| Material seals | NBR |
| Material housing | High alloy steel |