

shock absorber DYEF-M10-Y1F

Part number: 548374

FESTO



Data sheet

Feature	Value
Size	M10
Stroke	3.7 mm
Cushioning	Pneumatic cushioning with fixed metallic stop
Assembly position	Any
Position detection	No
Max. impact speed	0.8 m/s
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Cushioning length	3.7 mm
Max. energy consumption per stroke	0.06 J
Product weight	19.7 g
Mounting type	with lock nut
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	High alloy steel