


axial kit EAMM-A-E48-57A

Part number: 550970

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	7.5 Nm
Product weight	540 g
Interface code, actuator	E48A
Interface code, motor in	57A
Materials note	Conforms to RoHS