

# fibre-optic cable SOOC-TB-P-M3-2-R10-S4

Part number: 552820

FESTO

Suitable for SOE4 fibre-optic units.



## Data sheet

Feature	Value
Materials note	Contains PWIS substances
Measurement method	Through-beam sensor
Minimal object diameter	0.05 mm
Fibre-optic cable - special feature	Precision
Working range	30 mm
Ambient temperature	-55 ... 70 °C
Size, head	M3
Fibre optic cable length	2 m
Sleeve length	40 mm
Min. bending radius	10 mm
Max. tightening torque	1 Nm
Outside diameter	1 mm
Materials information, housing	High alloy steel, non-corrosive
Material information, fibre optic cable	PE
Protection class	IP66
Corrosion resistance classification CRC	1