


fibre-optic cable SOOC-TB-M4-2-R25-T1

Part number: 552826

FESTO

Suitable for SOE4 fibre-optic units.



Data sheet

Feature	Value
Materials note	Contains PWIS substances
Measurement method	Through-beam sensor
Minimal object diameter	0.35 mm
Fibre-optic cable - special feature	High temperature
Working range	400 mm
Ambient temperature	-55 ... 115 °C
Size, head	M4
Fibre optic cable length	2 m
Min. bending radius	25 mm
Max. tightening torque	2 Nm
Outside diameter	2.2 mm
Materials information, housing	High alloy steel, non-corrosive
Material information, fibre optic cable	PE
Protection class	IP66
Corrosion resistance classification CRC	1