

# micro filter

## MS9-LFM-N1-AUV-HF

Part number: 553056

FESTO

0.01 µm filter, metal bowl guard, high flow rate, fully automatic condensate drain, flow direction from left to right.



### Data sheet

Feature	Value
Series	MS
Size	9
Design structure	Fibre filter
Grade of filtration	0.01 µm
Condensate drain	fully automatic manual momentary-contact
Operating pressure	2 ... 12 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4]
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [1:7:2]
Max. standard flow rate for air quality class	7,800 l/min
Min. standard flow rate for air quality class	390 l/min
Filter efficiency	99.9999 %
Max. condensate volume	225 ml
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	5 ... 60 °C
Ambient temperature	5 ... 60 °C
Storage temperature	-10 ... 60 °C
Residual oil content	0.01 mg/m <sup>3</sup>
Mounting type	Line installation with accessories Optional
Assembly position	Vertical +/- 5°
Pneumatic connection, port 1	1 NPT
Pneumatic connection, port 2	1 NPT
Material housing	Aluminium die cast
Material of cover	PA
Material filter	Boron silicate fibre
Material bowl	Wrought Aluminium alloy
Material screen	PA
Material seals	NBR
Product weight	2,500 g