

bellows kit DADB-S1-12-S151-200

Part number: 553397

FESTO

For standard cylinders to ISO 6432



Data sheet

Feature	Value
Outside diameter	22 mm
Size	12
Stroke range	151 ... 200 mm
Piston rod extension	59 mm
Design	Round
Assembly position	Any
Design structure	Bellows kit with ducted exhaust air
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5a
Resistance to media	Dust Chippings Oils Grease Gasolines
Ambient temperature	-10 ... 80 °C
Product weight	16 g
Mounting type	With threaded pin with internal (female) thread
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material adapter components	PA-reinforced
Material seals	NBR
Material bellows	NBR
Material threaded pin	High alloy steel, non-corrosive