

bellows kit DADB-S1-16-S10-50

Part number: 553399

FESTO

For standard cylinders to ISO 6432



Data sheet

Feature	Value
Outside diameter	22 mm
Size	16
Stroke range	10 ... 50 mm
Piston rod extension	23 mm
Design	Round
Assembly position	Any
Design structure	Bellows kit with ducted exhaust air
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5a
Resistance to media	Dust Chippings Oils Grease Gasolines
Ambient temperature	-10 ... 80 °C
Product weight	7 g
Mounting type	With threaded pin with internal (female) thread
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material adapter components	PA-reinforced
Material seals	NBR
Material bellows	NBR
Material threaded pin	High alloy steel, non-corrosive