


plug
NECC-L1G8-C1

Part number: 553860

FESTO



Data sheet

Feature	Value
Operating voltage range AC	300 V
Permissible current load	10 A
Terminal cross-section	0.2 ... 2.5 mm ²
Ambient temperature	-25 ... 100 °C
Degree of contamination	3
Corrosion resistance classification CRC	0 - No corrosion stress
Material housing	PBT