

# axial kit EAMM-A-S62-140A

Part number: 558168

FESTO

Suitable for electric drives.



## Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	17 Nm
Product weight	2,870 g
Interface code, actuator	S62
Interface code, motor in	140A
Materials note	Conforms to RoHS