


coupling EAMC-30-32-6-6

Part number: 558312

FESTO



Data sheet

| Feature | Value |
|------------------------|------------------------|
| Holder diameter 1 | 6 mm |
| Holder diameter 2 | 6 mm |
| Size | 30 |
| Nominal length | 32 mm |
| Assembly position | Any |
| Max. speed | 8,000 1/min |
| PWIS conformity | VDMA24364-B2-L |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 ... 60 °C |
| Mass moment of inertia | 5.87 kgmm ² |
| Transferable torque | 6.5 Nm |
| Product weight | 48 g |
| Materials note | Conforms to RoHS |