


# axial kit EAMM-A-K38-87A

Part number: 560682

FESTO

Suitable for electric drives.



## Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	4.4 Nm
Product weight	380 g
Interface code, actuator	K38
Interface code, motor in	87A
Materials note	Conforms to RoHS