


sub-base VMPAL-AP-20-QS3/8"-2-T1

Part number: 561028

FESTO



Data sheet

| Feature | Value |
|---|---|
| Width | 21.2 mm |
| Length | 107.3 mm |
| Grid dimension | 21.2 mm |
| Valve size | 20 mm |
| Pressure zone separation | Duct 1 |
| Max. number of valve positions | 1 |
| Flow direction | reversible |
| Valve terminal structure | Valve sizes can be mixed |
| Max. number of solenoid coils | 2 |
| Operating pressure MPa | -0.09 ... 1 MPa |
| Operating pressure | -0.9 ... 10 bar |
| Pilot pressure MPa | 0.3 ... 0.8 MPa |
| Pilot pressure | 3 ... 8 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 3 - High corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 82.28 g |
| Pneumatic connection, port 2 | for tubing, 3/8" outside diameter |
| Pneumatic connection, port 4 | for tubing, 3/8" outside diameter |
| Materials note | Conforms to RoHS |
| Material of connecting plate | PA-reinforced |