


# coupling EAMC-16-20-3-6

Part number: 562671

FESTO



## Data sheet

Feature	Value
Holder diameter 1	3 mm
Holder diameter 2	6 mm
Size	16
Nominal length	20 mm
Assembly position	Any
Max. speed	10,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	0.28 kgmm <sup>2</sup>
Transferable torque	0.2 Nm
Product weight	8 g
Materials note	Conforms to RoHS