



# pressure gauge PAGN-26-232P-P10

Part number: 563731

FESTO

With display unit in bar and psi.



## Data sheet

Feature	Value
Indicating range [bar]	0 ... 16 bar
Display range	0 ... 232 psi
Nominal size of pressure gauge	26
Design structure	Bourdon-tube pressure gauge
Mounting type	Line installation
Operating medium	Inert gases Neutral fluids
Operating pressure MPa	0 ... 1.6 MPa
Operating pressure	0 ... 16 bar 0 ... 232 psi
Alternating load factor	0.66
Measurement accuracy class	4
Protection class	IP43
Medium temperature	-20 ... 60 °C
Ambient temperature	-20 ... 60 °C
PWIS conformity	VDMA24364-B1/B2-L
Materials note	Conforms to RoHS
Position of connection	Rear side central
Pneumatic connection	Cartridge 10 mm
Materials in contact with media	Brass
Material of threaded plug	Brass
Material housing	PA
Material screen	PS
Housing colour	Black
Product weight	15 g
Note on operating and pilot medium	No acetylene No oxygen
Scale	Double scale bar (inner scale) psi (outer scale)