


blinking plate VABB-L1-10-S

Part number: 566462
★ Core product range

FESTO



Data sheet

Feature	Value
Grid dimension	10.5 mm
Operating pressure MPa	-0.09 ... 1 MPa
Operating pressure	-0.9 ... 10 bar
Authorisation	RCM Mark c UL us - Recognized (OL)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Product weight	10 g
Materials note	Conforms to RoHS
Material cover plate	PA