

Plastic tubing PLN-5/16-BL-150-CB

Part number: 569916

FESTO

highly resistant to chemicals and hydrolysis.

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

Feature	Value
Outer diameter, inches	5/16
Bending radius relevant for flow rate	0.164 Fuß
Min. bending radius	0.082 Fuß
Temperature dependent operating pressure	-14.4 ... 203 Psi
Certificate issuing department	TZW
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Food safety	to manufacturer's declaration
Ambient temperature	-22 ... 176 °F
Authorisation	Drinking water KTW-A Drinking water W 270
Product weight according to length	0.231 oz/ft
Colour	blue
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS Free of copper and PTFE
Materials information for tubing	PE