

# plastic tubing PLN-3/8-BL-150-CB

Part number: 569917

FESTO

highly resistant to chemicals and hydrolysis.



## Data sheet

Feature	Value
Outer diameter, inches	3/8
Bending radius relevant for flow rate	0.187 ft
Min. bending radius	0.115 ft
Temperature dependent operating pressure	-14.4 ... 203 Psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
PWIS conformity	VDMA24364-B1/B2-L
Food-safe	See Supplementary material information
Ambient temperature	-22 ... 176 °F
Product weight according to length	0.403 oz/ft
Pneumatic connection	For push-in connector outside diameter 3/8"
Colour	blue
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS
Material tubing	PE