

Bellows kit EADB-V1-32-S101-200

Part number: 570263

FESTO



Data sheet

Feature	Value
Outside diameter	46 mm
Size	32
Stroke range	101 ... 200 mm
Piston rod extension	74 mm
Design	Round
Assembly position	Any
Design structure	Bellows kit with ducted exhaust air
Corrosion resistance classification CRC	3
Resistance to media	Dust Chippings Oils Grease Gasolines
Protection class	IP65 to IEC 60529
Ambient temperature	-10 ... 80 °C
Moving mass	66 g
Product weight	108 g
Mounting type	slip-on With threaded pin
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Note on materials: Adapter components	Wrought Aluminium alloy Anodised
Materials information for seals	NBR
Note on materials: Bellows	NBR
Threaded stud material information	High alloy steel, non-corrosive