

# Bellows kit EADB-V1-63-S401-500

Part number: 570275

FESTO



## Data sheet

| Feature                                 | Value  |
|---|--|
| Outside diameter                        | 93 mm  |
| Size                                    | 63   |
| Stroke range                            | 401 ... 500 mm                                   |
| Piston rod extension                    | 117 mm   |
| Design                                  | Round  |
| Assembly position                       | Any  |
| Design structure                        | Bellows kit<br>with ducted exhaust air           |
| Corrosion resistance classification CRC | 3  |
| Resistance to media                     | Dust<br>Chippings<br>Oils<br>Grease<br>Gasolines |
| Protection class                        | IP65<br>to IEC 60529                             |
| Ambient temperature                     | -10 ... 80 °C                                    |
| Moving mass                             | 287 g  |
| Product weight                          | 397 g  |
| Mounting type                           | slip-on<br>With threaded pin                     |
| Pneumatic connection                    | G1/4   |
| Materials note                          | Conforms to RoHS                                 |
| Note on materials: Adapter components   | Wrought Aluminium alloy<br>Anodised              |
| Materials information for seals         | NBR  |
| Note on materials: Bellows              | NBR  |
| Threaded stud material information      | High alloy steel, non-corrosive                  |