

plastic tubing PAN-MF-12X1,5-SW

Part number: 570361

FESTO



Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	70 mm
Inside diameter	9 mm
Min. bending radius	50 mm
Conforms to standard	DIN 73378-PA12-PHL
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 ... 1.9 MPa
Temperature dependent operating pressure	-0.95 ... 19 bar
Temperature-dependent operating pressure	-13.775 ... 275.5 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Mineral oil
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-60 ... 100 °C
Product weight according to length	0.051 kg/m
Pneumatic connection	For push-in connector outside diameter 12 mm
Colour	Black
Shore hardness	D 65 +/-3
Materials note	Conforms to RoHS
Material tubing	Polyamide 12