Plastic tubing
PAN-M-8X1-GN

Part number: 572088

FESTO

Data sheet

Feature	Value
Outside diameter	8 mm
Bending radius relevant for flow rate	50 mm
Inside diameter	6 mm
Min. bending radius	35 mm
Temperature dependent operating pressure	-0.95 ... 26 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-60 ... 100 °C
Product weight according to length	0.022 kg/m
Colour	green
Shore hardness	D 65 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	Polyamide 12