

Plastic tubing PAN-M-10X1,25-NT

Part number: 572089

FESTO



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	65 mm
Inside diameter	7.5 mm
Min. bending radius	45 mm
Temperature dependent operating pressure	-0.95 ... 26 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Ambient temperature	-60 ... 100 °C
Product weight according to length	0.035 kg/m
Colour	neutral
Shore hardness	D 65 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	Polyamide 12