

# Fixed restrictor set VMPA1-FT-NW0.3-1.7

Part number: 572543

FESTO



## Data sheet

| Feature  | Value   |
|--|---|
| Valve function                                       | Throttle function   |
| Pneumatic connection, port 1                         | Sub-base  |
| Standard nominal flow rate in flow control direction | 3.5 ... 115 l/min   |
| Operating pressure                                   | -0.9 ... 10 bar   |
| Ambient temperature                                  | -5 ... 60 °C  |
| Nominal size   | 0.3 ... 1.7 mm  |
| Assembly position                                    | Any   |
| Operating medium                                     | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                   | Lubricated operation possible (subsequently required for further operation) |
| PWIS conformity                                      | VDMA24364-B1/B2-L   |
| Storage temperature                                  | -20 ... 40 °C   |
| Medium temperature                                   | -5 ... 60 °C  |
| Materials note                                       | Conforms to RoHS  |
| Material bracket                                     | POM   |
| Material hollow bolt                                 | Wrought Aluminium alloy   |